

Temperature calibrator TP M255S

TP Solid // Calibration bath // Room temperature...255 °C // RT...491 °F



TP M255S



Highlights

- Very easy operation with 4-button control and integrated reference temperature sensor
- PC interface with connection cable to USB for use with SIKA calibration software
- Low weight and stable handle for easy transport
- Optional accessory: Transport case with or without trolley
- Especially suitable for calibration of devices under test with special sensor geometry. DUTs are simply immersed in the calibration liquid, no calibration insert with specific bore hole pattern is required.

TP Solid

With the temperature calibrators of the TP Solid series, the main focus is on **flexibility**: In addition to **dry block calibrators**, they also include **calibration baths**, with which almost any temperature sensor can be calibrated irrespective of its shape. Both can be operated **easily and intuitively**. When being used as fluid bath calibrator, the temperature sensors are directly immersed into the calibration liquid. This creates a direct temperature link

between the calibrator and the devices under test without insulating air gap. All TP Solid temperature calibrators are additionally equipped with a **serial interface for computer-assisted monitoring** of the calibration process. This flexibility in combination with the easy operation make the TP Solid series ideal for **use in machinery and plant engineering**.

SIKA temperature calibrators

Temperature calibrators are used for the verification of the functionality and calibration of temperature measuring devices and temperature sensors. As the sole German manufacturer of these devices, we develop and produce our "Made in Germany" temperature calibrators with a special focus on **long-term reliability** and **utmost accuracy** in combination with **easy operation**. We can rely on more than 40 years of experience in doing this: SIKA's **first dry block temperature calibrator** was launched all the way back in 1980.

Every SIKA temperature calibrator is meticulously tested for **accuracy** and **stability**. This is attested by our standard calibration certificate, which we issue with every temperature calibrator, or by means of an optional DAKkS calibration certificate [German accreditation body]. This is to guarantee that you receive a **perfect product** which can be traced back to national and international temperature measurement standards.

Features

Easy operation

- The TP M255S can be operated with only four buttons: Two arrow buttons for setting the target temperature, one button for confirmation and one return button
- Thus, temperatures can be set as easily as, for example, in the air conditioning system in your car
- Any operational errors can be nearly excluded. You do not need any specifically trained staff or time-consuming briefings



5-Year Warranty: Low Maintenance, Comprehensive Service!

With regular service and adherence to the SIKA recalibration recommendation, you receive a 5-year warranty.

- Instead of annual recalibration, recalibration is only necessary every 500 operating hours or every three years thanks to long-lasting SIKA technology.
- This results in only 1/3 of the usual maintenance costs.
- Significant reduction in the total cost of ownership.



Technical data

TP M255S		
Temperature range	Room temperature...255 °C	Room temperature...491 °F
Calibration volume	Ø 60 x 170 mm	
Calibration bath		
Accuracy	±0.2 °C	±0.36 °F
Temperature stability	±0.05 °C	±0.09 °F
Resolution of the temperature display	0.01 °C in the range -9.99...99.99 °C, else 0.1 °C	0.01 °F in the range -9.99...99.99 °F, else 0.1 °F
Reference temperature sensor	internal, fixed installation	
Interface	RS485 (calibrator) to USB (PC)	
Connectivity	MODBUS	
Dimensions		
→ Width	150 mm	
→ Height	330 + 70 mm	
→ Depth	270 mm	
Weight	Approx. 7.5 kg	
Power supply	110...115 V 60 Hz / 230 V 50 Hz	
Power consumption	Approx. 1000 W	
Display		
Display	2-line, 4-digit digital display, red / green, unit °C / °F	
Approvals		

Article numbers

To order a complete calibrator, you need two article numbers:

1. Calibrator
2. Calibration insert

In addition, depending on your individual calibration requirements, you can order additional calibration inserts, necessary certificates and other accessories.

1. Calibrator					
Temperature range	Function	Calibration insert [mm]	Power supply	Article number	
Room temperature...255 °C	RT...491 °F	Calibration bath	Ø 60 x 170	100...230 V	EPMB250S601503

Notice: Every "linearisation" article number with 13 digits starts with "EK1", while the following letters ("short designation") indicate the selected calibration function. You may also select several functions of one category. Please indicate the calibration functions in alphabetical order and fill in any possibly remaining positions with "0".

2. Linearisation											
Calibration function	Calibration insert / calibration medium			Reference temperature sensor				Short designation			
Calibration bath (Direct filling)	20 cSt	7...220 °C	44.6...428 °F	internal				R			
	50 cSt	50...270 °C	122...518 °F	internal				T			
Example article number linearisation											
Function:		1	2	3	4	5	6	7	8	9	10
Article number:	EK1	T	0	0	0	0	0	0	0	0	0

3. Calibration certificate - Select your calibration certificates as needed		Article number
Each calibrator is already delivered with a standard calibration certificate (3 test points).		
SIKA works calibration certificate (similar to standard certificate + marking on the calibrator), 1st calibrator function		EKTPWP1FKT
SIKA works calibration certificate (similar to standard certificate + marking on the calibrator), 2nd calibrator function		EKTPWP2FKT
DAkKS calibration certificate (3 test points + measurement uncertainty determination) for 1st calibrator function		EKTPDAKKS1FKT
DAkKS calibration certificate (3 test points + measurement uncertainty determination) for 2nd calibrator function		EKTPDAKKS2FKT
Each additional test point DAkKS calibration certificate		EKTPDAKKSZUSP

4. Accessories		Article number
Transport case without trolley		EZTPKOFFER20
Transport case with trolley		EZTPKOFFER20TG
Tripod (holder for devices under test)		EZTPMSG0000000
Calibration liquid (silicone oil), 50cSt		EZSÖ0500000000
PC software		EZ999999999971
PC connection cable: temperature calibrator (RS485) to USB		EZ170000000002

Overview of SIKA temperature calibrators

Our series: Basic. Solid. Premium.

- **Dry block calibrators** of the **TP Basic** series impress with their **uncomplicated operation** and **high cost-effectiveness**. They are particularly suitable for use on ships or in industrial applications.
- Equipped with a **PC interface**, the **dry block calibrators** and **calibration baths** of the **TP Solid** series cover a wide temperature range with high accuracy.
- For the highest demands on accuracy and flexibility: The dry-block and multi-function temperature calibrators of the **TP Premium** series represent the pinnacle of our technical development. Equipped with an **integrated touch screen**, a **PC interface**, an **external reference sensor** and **integrated measuring instrument**, this series offers **extreme accuracies** for **all calibration tasks**.

Temperature range (RT=Room temperature)	Function	Accuracy		Features	Block dimensions [Ø mm x depth mm]	Type
-55 °C ... 200 °C -67 °F ... 392 °F	Dry block	±0.4 °C	±0.72 °F	TP Basic	28 x 150	TP 17200
	Dry block	±0.2 °C	±0.36 °F	TP Solid	28 x 150	TP 17200S
	Dry block	±0.1 °C	±0.18 °F	TP Premium	28 x 150	TP 37200E.2
-35 °C ... 155 °C -31 °F ... 311 °F	Calibration bath	±0.1 °C	±0.18 °F	TP Solid	60 x 170	TP M165S
-35 °C ... 165 °C -31 °F ... 329 °F	Dry block	±1 °C	±1.8 °F	TP Basic	28 x 150	TP 17165M
	Dry block	±0.4 °C	±0.72 °F	TP Basic	28 x 150	TP 17165
	Dry block	±0.2 °C	±0.36 °F	TP Solid	28 x 150	TP 17165S
	Dry block	±0.1 °C	±0.18 °F	TP Premium	28 x 150	TP 37165E.2
	Dry block Air Shield Insert Calibration bath Infrared Surface	±0.1 °C ±0.07 °C ±0.19 °C ±0.5 °C ±1 °C	±0.18 °F ±0.126 °F ±0.342 °F ±0.9 °F ±1.8 °F	TP Premium	60 x 170	TP 3M165E.2
-30 °C ... 165 °C -22 °F ... 329 °F	Dry block	±0.4 °C	±0.72 °F	TP Basic	60 x 150	TP 17166
	Dry block	±0.2 °C	±0.36 °F	TP Solid	60 x 150	TP 17166S
-10 °C ... 100 °C 14 °F ... 212 °F	Dry block	±0.05 °C	±0.09 °F	TP Solid	7 x 6.5 x 150	TP 17Zero
RT ... 200 °C RT ... 392 °F	Dry block	±1 °C	±1.8 °F	TP Basic	18 x 150	TP 18200E
RT ... 255 °C RT ... 491 °F	Calibration bath	±0.2 °C	±0.36 °F	TP Solid	60 x 170	TP M255S
	Dry block Air Shield Insert Calibration bath Infrared Surface	±0.25 °C ±0.08 °C ±0.18 °C ±0.5 °C ±1 °C	±0.45 °F ±0.144 °F ±0.324 °F ±0.9 °F ±1.8 °F	TP Premium	60 x 170	TP 3M255E.2
	Dry block	±0.6 °C	±1.08 °F	TP Basic	60 x 150	TP 17450
	Dry block	±0.3 °C	±0.54 °F	TP Solid	60 x 150	TP 17450S
RT ... 450 °C RT ... 842 °F	Dry block Air Shield Insert Infrared Surface	±0.25 °C ±0.2 °C ±0.5 °C ±1 °C	±0.45 °F ±0.36 °F ±0.9 °F ±1.8 °F	TP Premium	60 x 150	TP 37450E.2
	Dry block	±1 °C	±1.8 °F	TP Basic	28 x 150	TP 17650M
	Dry block	±0.8 °C	±1.44 °F	TP Basic	28 x 150	TP 17650
RT ... 650 °C RT ... 1202 °F	Dry block	±1.2 °C	±2.16 °F	TP Basic	13.5 x 110	TP Basic Marine
	Dry block	±0.4 °C	±0.72 °F	TP Solid	28 x 150	TP 17650S
RT ... 700 °C RT ... 1292 °F	Dry block Air Shield Insert	±0.43 °C ±0.27 °C	±0.744 °F ±0.486 °F	TP Premium	29 x 150	TP 37700E.2
	Dry block	±1 °C	±1.8 °F	TP Basic	18 x 100	TP 18850E

Subject to technical modifications and errors